SPARK

silentlab

Give your working environment the spark it needs. SPARK is our first acoustic meeting room with increased mechanical resistance, yet it still retains maximum functionality and elegant curves. It is easy to maintain and holds up even under the most difficult conditions. It performs beautifully for example in production halls or public areas.



Technical details

1110 × 2226 × 930 mm / 43.7 × 87.6 × 36.6 in exterior dimensions (w x h x d)

interior dimensions (w × h × d) 850 × 2057 × 864 mm / 33.4 × 80.9 × 34 in

350 kg / 771 lb weight

918 × 2075 mm / 36.1 × 81.7 in door dimensions

door opening clear dimensions 908 × 2055 mm / 35.7 × 80.9 in

lef1 door opens

glass doors sound-insulating glass sound-insulating glass glass walls

sandwich panel with acoustic filling solid walls ceiling sandwich panel with acoustic filling sandwich panel with acoustic filling, flooring

carpet (anthracite grey)

glass wall frame

and door handle

beech (black varnish)

sound attenuation speech level reduction Ds,a = 32 dB (class A)*1

ventilation standard air flow: 120 m³/h

maximum air flow: 341 m³/h

lighting LED, chromaticity temperature 4200 K

in operation 45 W*2 energy consumption

in standby 1 W

220-240 V, 50/60 Hz, 10 A power

desk $660 \times 320 \times 27 \text{ mm} / 23.6 \times 12.6 \times 1 \text{ in,}$

height 1053 mm - standing option, table in the middle of the wall.

electric socket (1x), ventilation, motion sensor, desk standard equipment

LED lighting, control panel for lighting and air ventilation

refer to the pricelist optional equipment

material lines - interior

and seating

decorative fabric Bombay 36 *3



BO36

color options of cladding - exterior

certification

powder coated steel - fine texture



CE

environmental product profile

This product has an Environmental Product Declaration (EPD*4) prepared in accordance with ISO 14025 and the implementing standards ISO 14040, ISO 14044, and EN 15804.

- *1 ISO 23351:1:2020 Acoustics Measurement of speech level reduction of furniture ensembles and enclosures Part 1: Laboratory method.
- *2 Consumption without attached appliances.
- *3 Product specifications apply when using standard materials. To ensure optimal performance, the product is designed to work with carefully selected and tested materials. Using materials not specified in the SilentLab material selection may affect acoustic properties and functionality.
- ^{*4} The EPD provides summary information on the potential environmental impacts of the product throughout its entire life cycle.

All intellectual property rights ("Rights"), whether registered or not, relating to any content, texts, photographs, images, logos, instructions, designs, technical solutions, etc. ("Content") are the property of SilentLab s.r.o. ("Owner") and any interference with these Rights to any Content or part thereof without the prior express and written consent of the Owner is not permitted. Any use of the Content not expressly authorized in writing in advance, with the exception of internal and non-commercial use of the unmodified Content for the purposes of the customer's own order, is considered an infringement of the Owner's Rights. In particular (not exclusively), any reproduction, change, addition, merger or other modification of the Content is prohibited without the prior express written consent of the Owner

The final product configuration may differ from the versions shown in the photographs



